

# MACIII Performance - Maintenance Schedule

Maintenance schedule vers. 1.2.0

User level

	Part description	Total lamp hours																																	
		750 hrs	1500 hrs	2250 hrs	3000 hrs	3750 hrs	4500 hrs	5250 hrs	6000 hrs	6750 hrs	7500 hrs	8250 hrs	9000 hrs	9750 hrs	10500 hrs	11250 hrs	12000 hrs	12750 hrs	13500 hrs	14250 hrs	15000 hrs	15750 hrs	16500 hrs	17250 hrs	18000 hrs										
<b>F I X T U R E  H E A D</b>	<b>Head - general</b>	C	C	C	Contact Martin Professional Aps	C	C	C	Contact Martin Professional Aps	C	C	C	Contact Martin Professional Aps	C	C	C	Contact Martin Professional Aps	C	C	C	Contact Martin Professional Aps	C	C	C	Contact Martin Professional Aps	C	C	C	Contact Martin Professional Aps						
	Lamp	R & A	R & A	R & A		R & A	R & A	R & A		R & A	R & A	R & A		R & A	R & A	R & A		R & A	R & A	R & A		R & A	R & A	R & A		R & A	R & A	R & A		R & A	R & A	R & A			
	Air Filters	C	C	C		C	C	C		C	C	C		C	C	C		C	C	C		C	C	C		C	C	C		C	C	C	C	C	C
	<b>Color mixing module</b>	C	C	C		C	C	C		C	C	C		C	C	C		C	C	C		C	C	C		C	C	C		C	C	C	C	C	C
	<b>Framing module</b>	C	C	C		C	C	C		C	C	C		C	C	C		C	C	C		C	C	C		C	C	C		C	C	C	C	C	C
	<b>Zoom focus module</b>	C	C	C		C	C	C		C	C	C		C	C	C		C	C	C		C	C	C		C	C	C		C	C	C	C	C	C
	Lenses	C	C	C		C	C	C		C	C	C		C	C	C		C	C	C		C	C	C		C	C	C		C	C	C	C	C	C
<b>B A S E</b>	<b>Base - general</b>	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C							
	Base air filter	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C							
	<b>Display module</b>	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C							
	<b>Power unit</b>	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C							

Conditions	
Ambient temperature	40°C
Voltage / frequency	Within specified range for the product

Code	
I	Inspect
R	Replace
C	Clean
L	Lubricate
A	Adjust
U	Update